

NSF LISTED

LGH SERIES



The LGH Series is a Two-way Ball Valve. It has an operating pressure of 150 psi, and a working temperature up to 140° F. Available in variations of Female and Male GHT, and Female and Male NPT with combinations of these sizes: 3/8 inch, 1/2 inch, and 3/4 inch; all with a .625 through hole. Materials available are Gray PVC and Polypropylene. The PVC and Polypropylene materials are used for chemical resistance applications and are NSF Standard 61 Certified. PVC with EPDM seals are standard. Other seal options are Buna-N and Viton®. Panel Mounts are not available.

SKU	Description
LGH-34F12M	3/4 FNPT by 1/2 MNPT Ball Valve
LGH-34F34MGH	3/4 FNPT by 3/4 MGH Ball Valve
LGH-34F6B	3/4 FNPT by 3/8 Barb Ball Valve
LGH-34F-B	3/4 FNPT by 3/4 FNPT PVC/Buna Ball Valve
LGH-34FF	3/4 FNPT by 3/4 FNPT Ball Valve
LGH-34FGH34F	3/4 FGH by 3/4 FNPT Ball Valve
LGH-34FGH34M	3/4 FGH by 3/4 MNPT Ball Valve
LGH-34FGH6B	3/4 FGH by 3/8 Barb Ball Valve
LGH-34FGH8M	3/4 FGH by 1/2 MNPT Ball Valve
LGH-34FGHMGH	3/4 FGH by 3/4 MGH Ball Valve
LGH-34FM	3/4 FNPT by 3/4 MNPT Ball Valve
LGH-34FM-E	3/4 FNPT to 3/4 MNPT PVC/EPDM Ball Valve
LGH-34FM-PP-E	3/4 FNPT to 3/4 MNPT Bk Polypropylene/EPDM Ball Valve

GEN1 SERIES BARBED FITTINGS



GEN1 Series, manufactured by Pneuline, are single barbed plastic fittings without a parting line on the barb. These can be molded from:

Natural Nylon * NN

White Nylon * WN

Black Nylon BN

Glass-Filled Black Nylon GFBN

PVDF USP Class 6 * PVDF Available in Gray.

Natural Polypropylene USP Class 6 * NP

Acetal NSF 51/61 * AC

High Density Polyethylene HDPE

Polycarbonate USP Class 6 * PC

Radiation Stable Polycarbonate * RSPC

Other materials are available to comply to customer specifications and requirements. Available in Tees, Elbows and Straight connections. * Items can be run in a class 7 clean room environment.

Some materials have specific characteristics such as:

- Black Nylon is UV resistant, making it good for outdoor use.
- Glass-Filled Nylon is stronger than regular nylon and doesn't absorb liquids, making it good for use where water is prevalent. Glass-Filled Nylon is also good for outdoor motor vehicles, such as motorcycles, boats, and cars.
- PVDF, Polypropylene, and Polycarbonate are all Class 6 USP and are good for medical and bio-pharmaceutical applications. These materials are bovine free.
- Acetal is NSF 51/61 listed and can be used for potable water and food applications.

The GEN1 Series is available in Elbow, Tee, and Straight configurations with barb sizes of: 1/16, 1/8, 3/16 inch, 1/4 inch, 3/8 inch.

[View our Flyer Here](#)

SKU	Description
GEN1-T-1B	1/16 inch Single Barb Tee
Gen1-T-2B	1/8 inch Single Barb Tee
Gen1-T-3B	3/16 Single Barb Tee
GEN1-T-4B	1/4 inch Single Barb Tee
GEN1-T-6B	3/8 inch Single Barb Tee
Gen1-L-1B	1/16 inch Barbed Elbow
Gen1-L-2B	1/8 Inch Barbed Elbow

SKU	Description
GEN1-L-3B	3/16 inch Single Barb Elbow
GEN1-L-4B	1/4 inch Single Barb Elbow
GEN1-L-6B	3/8 inch Single Barb Elbow
Gen1-S-1B	1/16 Inch Single Barb Straight
Gen1-S-2B	1/8 inch Single Barb Straight
GEN1-S-3B	3/16 inch Single Barb Straight
GEN1-S-4B	1/4 inch Single Barb Straight
GEN1-S-6B	3/8 inch Single Barb Straight

SKU	Description	Description
Fitting for tube ID	Natural PVDF	Gray PVDF
GEN1-T-1B NK	1/16 inch Single Barb Tee PVDF	1/16 inch Single Barb Tee GK
Gen1-T-2B NK	1/8 inch Single Barb Tee PVDF	1/8 inch Single Barb Tee GK
Gen1-T-3B NK	3/16 Single Barb Tee PVDF	3/16 Single Barb Tee GK
GEN1-T-4B NK	1/4 inch Single Barb Tee PVDF	1/4 inch Single Barb Tee GK
GEN1-T-6B NK	3/8 inch Single Barb Tee PVDF	3/8 inch Single Barb Tee GK
Gen1-L-1B NK	1/16 inch Barbed Elbow PVDF	1/16 inch Barbed Elbow GK
Gen1-L-2B NK	1/8 Inch Barbed Elbow PVDF	1/8 Inch Barbed Elbow GK
GEN1-L-3B NK	3/16 inch Single Barb Elbow PVDF	3/16 inch Single Barb Elbow GK
GEN1-L-4B NK	1/4 inch Single Barb Elbow PVDF	1/4 inch Single Barb Elbow GK
GEN1-L-6B NK	3/8 inch Single Barb Elbow PVDF	3/8 inch Single Barb Elbow GK
Gen1-S-1B NK	1/16 Inch Single Barb Straight PVDF	1/16 Inch Single Barb Straight GK
Gen1-S-2B NK	1/8 inch Single Barb Straight PVDF	1/8 inch Single Barb Straight GK
GEN1-S-3B NK	3/16 inch Single Barb Straight PVDF	3/16 inch Single Barb Straight GK
GEN1-S-4B NK	1/4 inch Single Barb Straight PVDF	1/4 inch Single Barb Straight GK
GEN1-S-6B NK	3/8 inch Single Barb Straight PVDF	3/8 inch Single Barb Straight GK

SKU	Description	Description	Description	Description
Fitting for tube ID	Natural Nylon NN	White Nylon WN	Black Nylon BN	30% Glass Filled Black Nylon GFBN
GEN1-T-1B	1/16 inch Single Barb Tee NN	1/16 inch Single Barb Tee WN	1/16 inch Single Barb Tee BN	1/16 inch Single Barb Tee GFBN
GEN1-T-2B	1/8 inch Single Barb Tee NN	1/8 inch Single Barb Tee WN	1/8 inch Single Barb Tee BN	1/8 inch Single Barb Tee GFBN
GEN1-T-3B	3/16 Single Barb Tee NN	3/16 Single Barb Tee WN	3/16 Single Barb Tee BN	3/16 Single Barb Tee WN
GEN1-T-4B	1/4 inch Single Barb Tee NN	1/4 inch Single Barb Tee WN	1/4 inch Single Barb Tee BN	1/4 inch Single Barb Tee GFBN

SKU	Description	Description	Description	Description
GEN1-T-6B	3/8 inch Single Barb Tee NN	3/8 inch Single Barb Tee WN	3/8 inch Single Barb Tee BN	3/8 inch Single Barb Tee GFBN
GEN1-L-1B	1/16 inch Barbed Elbow NN	1/16 inch Barbed Elbow WN	1/16 inch Barbed Elbow BN	1/16 inch Barbed Elbow GFBN
GEN1-L-2B	1/8 Inch Barbed Elbow NN	1/8 Inch Barbed Elbow WN	1/8 Inch Barbed Elbow BN	1/8 Inch Barbed Elbow GFBN
GEN1-L-3B	3/16 inch Single Barb Elbow NN	3/16 inch Single Barb Elbow WN	3/16 inch Single Barb Elbow BN	3/16 inch Single Barb Elbow GFBN
GEN1-L-4B	1/4 inch Single Barb Elbow NN	1/4 inch Single Barb Elbow WN	1/4 inch Single Barb Elbow BN	1/4 inch Single Barb Elbow GFBN
GEN1-L-6B	3/8 inch Single Barb Elbow NN	3/8 inch Single Barb Elbow WN	3/8 inch Single Barb Elbow BN	3/8 inch Single Barb Elbow GFBN
GEN1-S-1B	1/16 Inch Single Barb Straight NN	1/16 Inch Single Barb Straight WN	1/16 Inch Single Barb Straight BN	1/16 Inch Single Barb Straight GFBN
Gen1-S-2B	1/8 inch Single Barb Straight NN	1/8 inch Single Barb Straight WN	1/8 inch Single Barb Straight BN	1/8 inch Single Barb Straight GFBN
GEN1-S-3B	3/16 inch Single Barb Straight NN	3/16 inch Single Barb Straight WN	3/16 inch Single Barb Straight BN	3/16 inch Single Barb Straight GFBN
GEN1-S-4B	1/4 inch Single Barb Straight NN	1/4 inch Single Barb Straight WN	1/4 inch Single Barb Straight BN	1/4 inch Single Barb Straight GFBN
GEN1-S-6B	3/8 inch Single Barb Straight NN	3/8 inch Single Barb Straight WN	3/8 inch Single Barb Straight BN	3/8 inch Single Barb Straight GFBN

DCE SERIES



The DCE Series is a rigid male Check Valve elbow made of Acetal that is NSF 51® certified and meets NSF 61® requirements. The available male threads are: 1/8 inch, 1/4 inch, and 3/8 inch. OD tubing sizes are 5/32 inch, 3/16 inch, 1/4 inch, 5/16 inch, 3/8 inch, and 1/2 inch. The working pressure at 77° F is 232 psi, and at 158° F it is 145 psi. The working temperature range is from 32° F to 158° F. It can be used for compressed air, inert gases, water, and other fluids.

SKU	Description
DCE-2M-14	1/8 MNPT by 1/4 OD Push-in Elbow Spring-loaded Check Valve
DCE-4M-14	1/4 MNPT by 1/4 OD Push-to Connect Elbow Check Valve
DCE-6M-14	3/8 MNPT by 1/4 OD Push-to Connect Elbow Check Valve

CR SERIES



The CR Series Plastic Multi-Barbed Fittings are reducing connectors with a standard Triple-Barb hose. Molded of either NSF Listed Natural Nylon, NSF Listed Black Polyethylene, FDA Listed Natural Polypropylene, FDA Listed Black Polypropylene, or Black Nylon. Sizes ranging from 1/8 inch to 1-1/2 inch.

SKU	Description
CR-4B2B	1/4 Multi Barb by 1/8 Multi Barb Reducer
CR-4B3B	1/4 Multi Barb by 3/16 Multi Barb Reducer
CR-4B532	1/4 Multi Barb by 5/32 Multi Barb Reducer
CR-5B2B	5/16 Multi Barb by 1/8 Multi Barb Reducer
CR-5B3B	5/16 Multi Barb by 3/16 Multi Barb Reducer
CR-6B4B	3/8 Multi Barb by 1/4 Multi Barb Reducer
CR-6B5B	3/8 Multi Barb by 5/16 Multi Barb Reducer
CR-6B8B	3/8 Multi Barb by 1/2 Multi Barb Reducer
CR-8B4B	1/2 Multi Barb by 1/4 Multi Barb Reducer
CR-8B6B	1/2 Multi Barb by 3/8 Multi Barb Reducer
CR-10B6B	5/8 Multi Barb by 3/8 Multi Barb Reducer
CR-10B8B	5/8 Multi Barb by 1/2 Multi Barb Reducer
CR-12B8B	3/4 Multi BarbX 1/2 Multi Barb Reducer



C MULTI-BARB EQUAL REDUCING CONNECTOR

The C Series are standard multi-barbed straight and reducing connectors. They are available in Black Nylon, NSF listed Natural Nylon and Black Polyethylene, and FDA listed Natural and Black Polypropylene. A range of barb sizes from 1/8 inch to 1-1/2 inch are available.



SKU	Description
C-2B2B-NN-NSF	1/8 inch NSF Natural Nylon Multi-Barbed Connector
C-2B2B-BPE-NSF	1/8 inch NSF Black Polyethylene Multi-Barbed Connector
C-2B2B-NPP-FDA	1/8 inch FDA Natural Polypropylene Multi-Barbed Connector
C-2B2B-BPP-FDA	1/8 inch FDA Black Polypropylene Multi-Barbed Connector
C-2B2B-BN	1/8 inch Black Nylon Multi-Barbed Connector
C-3B3B-NN-NSF	3/16 inch NSF Natural Nylon Multi-Barbed Connector
C-3B3B-BPE-NSF	3/16 inch NSF Black Polyethylene Multi-Barbed Connector
C-3B3B-NPP-FDA	3/16 inch FDA Natural Polypropylene Multi-Barbed Connector
C-3B3B-BPP-FDA	3/16 inch FDA Black Polypropylene Multi-Barbed Connector
C-3B3B-BN	3/16 inch Black Nylon Multi-Barbed Connector

SKU	Description
C-4B4B-NN-NSF	1/4 inch NSF Natural Nylon Multi-Barbed Connector
C-4B4B-BPE-NSF	1/4 inch NSF Black Polyethylene Multi-Barbed Connector
C-4B4B-NPP-FDA	1/4 inch FDA Natural Polypropylene Multi-Barbed Connector
C-4B4B-BPP-FDA	1/4 inch FDA Black Polypropylene Multi-Barbed Connector
C-4B4B-BN	1/4 inch Black Nylon Multi-Barbed Connector
C-5B5B-NN-NSF	5/16 inch NSF Natural Nylon Multi-Barbed Connector
C-5B5B-BPE-NSF	5/16 inch NSF Black Polyethylene Multi-Barbed Connector
C-5B5B-NPP-FDA	5/16 inch FDA Natural Polypropylene Multi-Barbed Connector
C-5B5B-BPP-FDA	5/16 inch FDA Black Polypropylene Multi-Barbed Connector
C-5B5B-BN	5/16 inch Black Nylon Multi-Barbed Connector
C-6B6B-NN-NSF	3/8 inch NSF Natural Nylon Multi-Barbed Connector
C-6B6B-BPE-NSF	3/8 inch NSF Black Polyethylene Multi-Barbed Connector
C-6B6B-NPP-FDA	3/8 inch FDA Natural Polypropylene Multi-Barbed Connector
C-6B6B-BPP-FDA	3/8 inch FDA Black Polypropylene Multi-Barbed Connector
C-6B6B-BN	3/8 inch Black Nylon Multi-Barbed Connector
C-8B8B-NN-NSF	1/2 inch NSF Natural Nylon Multi-Barbed Connector
C-8B8B-BPE-NSF	1/2 inch NSF Black Polyethylene Multi-Barbed Connector
C-8B8B-NPP-FDA	1/2 inch FDA Natural Polypropylene Multi-Barbed Connector
C-8B8B-BPP-FDA	1/2 inch FDA Black Polypropylene Multi-Barbed Connector
C-8B8B-BN	1/2 inch Black Nylon Multi-Barbed Connector
C-10B10-NN-NSF	5/8 inch NSF Natural Nylon Multi-Barbed Connector
C-10B10B-BPE-NSF	5/8 inch NSF Black Polyethylene Multi-Barbed Connector
C-10B10B-NPP-FDA	5/8 inch FDA Natural Polypropylene Multi-Barbed Connector
C-10B10B-BPP-FDA	5/8 inch FDA Black Polypropylene Multi-Barbed Connector
C-10B10B-BN	5/8 inch Black Nylon Multi-Barbed Connector
C-12B12B-NN-NSF	3/4 inch NSF Natural Nylon Multi-Barbed Connector
C-12B12B-BPE-NSF	3/4 inch NSF Black Polyethylene Multi-Barbed Connector
C-12B12B-NPP-FDA	3/4 inch FDA Natural Polypropylene Multi-Barbed Connector
C-12B12B-BPP-FDA	3/4 inch FDA Black Polypropylene Multi-Barbed Connector
C-12B12B-BN	3/4 inch Black Nylon Multi-Barbed Connector
C-16B16B-NN-NSF	1 inch NSF Natural Nylon Multi-Barbed Connector
C-16B16B-BPE-NSF	1 inch NSF Black Polyethylene Multi-Barbed Connector
C-16B16B-NPP-FDA	1 inch FDA Natural Polypropylene Multi-Barbed Connector
C-16B16B-BPP-FDA	1 inch FDA Black Polypropylene Multi-Barbed Connector
C-16B16B-BN	1 inch Black Nylon Multi-Barbed Connector
C-20B20B-NN-NSF	1-1/4 inch NSF Natural Nylon Multi-Barbed Connector
C-20B20B-BPE-NSF	1-1/4 inch NSF Black Polyethylene Multi-Barbed Connector
C-20B20B-NPP-FDA	1-1/4 inch FDA Natural Polypropylene Multi-Barbed Connector
C-20B20B-BPP-FDA	1-1/4 inch FDA Black Polypropylene Multi-Barbed Connector
C-20B20B-BN	1-1/4 inch Black Nylon Multi-Barbed Connector

SKU	Description
C-24B24B-NN-NSF	1-1/2 inch NSF Natural Nylon Multi-Barbed Connector
C-24B24B-BPE	1-1/2 inch NSF Black Polyethylene Multi-Barbed Connector
C-24B24B-NPP-FDA	1-1/2 inch FDA Natural Polypropylene Multi-Barbed Connector
C-24B24B-BPP-FDA	1-1/2 inch FDA Black Polypropylene Multi-Barbed Connector
C-24B24B-BN	1-1/2 inch Black Nylon Multi-Barbed Connector
C-4B2B-NN-NSF	1/4 inch by 1/8 inch NSF Natural Nylon Multi-Barbed Reducing Connector
C-4B2B-BPE-NSF	1/4 inch by 1/8 inch NSF Black Polyethylene Multi-Barbed Reducing Connector
C-4B2B-NPP-FDA	1/4 inch by 1/8 inch FDA Natural Polypropylene Multi-Barbed Reducing Connector
C-4B2B-BPP-FDA	1/4 inch by 1/8 inch FDA Black Polypropylene Multi-Barbed Reducing Connector
C-4B2B-BN	1/4 inch by 1/8 inch Black Nylon Multi-Barbed Reducing Connector
C-4B3B-NN-NSF	1/4 inch by 3/16 inch NSF Natural Nylon Multi-Barbed Reducing Connector
C-4B3B-BPE-NSF	1/4 inch by 3/16 inch NSF Black Polyethylene Multi-Barbed Reducing Connector
C-4B3B-NPP-FDA	1/4 inch by 3/16 inch FDA Natural Polypropylene Multi-Barbed Reducing Connector
C-4B3B-BPP-FDA	1/4 inch by 3/16 inch FDA Black Polypropylene Multi-Barbed Reducing Connector
C-4B3B-BN	1/4 inch by 3/16 inch Black Nylon Multi-Barbed Reducing Connector
C-4B532-NN-NSF	1/4 inch by 5/32 inch NSF Natural Nylon Multi-Barbed Reducing Connector
C-4B532-BPE-NSF	1/4 inch by 5/32 inch NSF Black Polyethylene Multi-Barbed Reducing Connector
C-4B532-NPP-FDA	1/4 inch by 5/32 inch FDA Natural Polypropylene Multi-Barbed Reducing Connector
C-4B532-BPP-FDA	1/4 inch by 5/32 inch FDA Black Polypropylene Multi-Barbed Reducing Connector
C-4B532-BN	1/4 inch by 5/32 inch Black Nylon Multi-Barbed Reducing Connector
C-5B2B-NN-NSF	5/16 inch by 1/8 inch NSF Natural Nylon Multi-Barbed Reducing Connector
C-5B2B-BPE-NSF	5/16 inch by 1/8 inch NSF Black Polyethylene Multi-Barbed Reducing Connector
C-5B2B-NPP-FDA	5/16 inch by 1/8 inch FDA Natural Polypropylene Multi-Barbed Reducing Connector
C-5B2B-BPP-FDA	5/16 inch by 1/8 inch FDA Black Polypropylene Multi-Barbed Reducing Connector
C-5B2B-BN	5/16 inch by 1/8 inch Black Nylon Multi-Barbed Reducing Connector
C-5B3B-NN-NSF	5/16 inch by 3/16 inch NSF Natural Nylon Multi-Barbed Reducing Connector
C-5B3B-BPE-NSF	5/16 inch by 3/16 inch NSF Black Polyethylene Multi-Barbed Reducing Connector
C-5B3B-NPP-FDA	5/16 inch by 3/16 inch FDA Natural Polypropylene Multi-Barbed Reducing Connector
C-5B3B-BPP-FDA	5/16 inch by 3/16 inch FDA Black Polypropylene Multi-Barbed Reducing Connector

SKU	Description
C-5B3B-BN	5/16 inch by 3/16 inch Black Nylon Multi-Barbed Reducing Connector
C-6B4B-NN-NSF	3/8 inch by 1/4 inch NSF Natural Nylon Multi-Barbed Reducing Connector
C-6B4B-BPE-NSF	3/8 inch by 1/4 inch NSF Black Polyethylene Multi-Barbed Reducing Connector
C-6B4B-NPP-FDA	3/8 inch by 1/4 inch FDA Natural Polypropylene Multi-Barbed Reducing Connector
C-6B4B-BPP-FDA	3/8 inch by 1/4 inch FDA Black Polypropylene Multi-Barbed Reducing Connector
C-6B4B-BN	3/8 inch by 1/4 inch Black Nylon Multi-Barbed Reducing Connector
C-6B5B-NN-NSF	3/8 inch by 5/16 inch NSF Natural Nylon Multi-Barbed Reducing Connector
C-6B5B-BPE-NSF	3/8 inch by 5/16 inch NSF Black Polyethylene Multi-Barbed Reducing Connector
C-6B5B-NPP-FDA	3/8 inch by 5/16 inch FDA Natural Polypropylene Multi-Barbed Reducing Connector
C-6B5B-BPP-FDA	3/8 inch by 5/16 inch FDA Black Polypropylene Multi-Barbed Reducing Connector
C-6B5B-BN	3/8 inch by 5/16 inch Black Nylon Multi-Barbed Reducing Connector
C-6B8B-NN-NSF	3/8 inch by 1/2 inch NSF Natural Nylon Multi-Barbed Reducing Connector
C-6B8B-BPE-NSF	3/8 inch by 1/2 inch NSF Black Polyethylene Multi-Barbed Reducing Connector
C-6B8B-NPP-FDA	3/8 inch by 1/2 inch FDA Natural Polypropylene Multi-Barbed Reducing Connector
C-6B8B-BPP-FDA	3/8 inch by 1/2 inch FDA Black Polypropylene Multi-Barbed Reducing Connector
C-6B8B-BN	3/8 inch by 1/2 inch Black Nylon Multi-Barbed Reducing Connector
C-8B4B-NN-NSF	1/2 inch by 1/4 inch NSF Natural Nylon Multi-Barbed Reducing Connector
C-8B4B-BPE-NSF	1/2 inch by 1/4 inch NSF Black Polyethylene Multi-Barbed Reducing Connector
C-8B4B-NPP-FDA	1/2 inch by 1/4 inch FDA Natural Polypropylene Multi-Barbed Reducing Connector
C-8B4B-BPP-FDA	1/2 inch by 1/4 inch FDA Black Polypropylene Multi-Barbed Reducing Connector
C-8B4B-BN	1/2 inch by 1/4 inch Black Nylon Multi-Barbed Reducing Connector
C-8B6B-NN-NSF	1/2 inch by 3/8 inch NSF Natural Nylon Multi-Barbed Reducing Connector
C-8B6B-BPE-NSF	1/2 inch by 3/8 inch NSF Black Polyethylene Multi-Barbed Reducing Connector
C-8B6B-NPP-FDA	1/2 inch by 3/8 inch FDA Natural Polypropylene Multi-Barbed Reducing Connector
C-8B6B-BPP-FDA	1/2 inch by 3/8 inch FDA Black Polypropylene Multi-Barbed Reducing Connector
C-8B6B-BN	1/2 inch by 3/8 inch Black Nylon Multi-Barbed Reducing Connector
C-8B6B-PVDF	1/2 inch by 3/8 inch PVDF Multi-Barbed Reducing Connector
C-10B6B-NN-NSF	5/8 inch by 3/8 inch NSF Natural Nylon Multi-Barbed Reducing Connector
C-10B6B-BPE-NSF	5/8 inch by 3/8 inch NSF Black Polyethylene Multi-Barbed Reducing Connector
C-10B6B-NPP-FDA	5/8 inch by 3/8 inch FDA Natural Polypropylene Multi-Barbed Reducing Connector

SKU	Description
C-10B6B-BPP-FDA	5/8 inch by 3/8 inch FDA Black Polypropylene Multi-Barbed Reducing Connector
C-10B6B-BN	5/8 inch by 3/8 inch Black Nylon Multi-Barbed Reducing Connector
C-10B8B-BPE-NSF	5/8 inch by 1/2 inch NSF Black Polyethylene Multi-Barbed Reducing Connector
C-10B8B-BPP-FDA	5/8 inch by 1/2 inch FDA Black Polypropylene Multi-Barbed Reducing Connector
C-10B8B-NN-NSF	5/8 inch by 1/2 inch NSF Natural Nylon Multi-Barbed Reducing Connector
C-10B8B-NPP-FDA	5/8 inch by 1/2 inch FDA Natural Polypropylene Multi-Barbed Reducing Connector
C-10B8B-BN	5/8 inch by 1/2 inch Black Nylon Multi-Barbed Reducing Connector
C-12B8B-NN-NSF	3/4 inch by 1/2 inch NSF Natural Nylon
C-12B8B-BPE-NSF	3/4 inch by 1/2 inch NSF Black Polyethylene
C-12B8B-NPP-FDA	3/4 inch by 1/2 inch FDA Natural Polypropylene
C-12B8B-BPP-FDA	3/4 inch by 1/2 inch FDA Black Polypropylene
C-12B8B-BN	3/4 inch by 1/2 inch Black Nylon

AT SERIES



The AT series is an MNPT by plastic triple barbed tee adapter. It is molded of NSF listed Natural Nylon, Black Nylon, and Black Polyethylene. Optional materials are FDA listed Natural Polypropylene and Black Polypropylene. MNPT threads sizes are 1/8 inch, 1/4 inch, 3/8 inch, 1/2 inch, 3/4 inch, and 1 inch. The barb sizes available are 1/4 inch, 3/8 inch, 1/2 inch, 3/4 inch, 5/8 inch, and 1 inch.

SKU	Description
AT-2M3B	1/8 MNPT to 3/16 Triple Barb Tee
AT-2M4B	1/8 MNPT to 1/4 Triple Barb Tee
AT-4M3B	1/4 MNPT to 3/16 Triple Barb Tee
AT-4M4B	1/4 MNPT to 1/4 Triple Barb Tee
AT-4M5B	1/4 MNPT to 5/16 Triple Barb Tee
AT-4M6B	1/4 MNPT to 3/8 Triple Barb Tee
AT-4M8B	1/4 MNPT to 1/2 Triple Barb Tee
AT-6M4B	3/8 MNPT to 1/4 Triple Barb Tee
AT-6M6B	3/8 MNPT to 3/8 Triple Barb Tee
AT-6M8B	3/8 MNPT to 1/2 Triple Barb Tee
AT-8M6B	1/2 MNPT to 3/8 Triple Barb Tee
AT-8M8B	1/2 MNPT to 1/2 Triple Barb Tee
AT-8M16B	1/2 MNPT to 1 inch Triple Barb Tee
AT-12M12B	3/4 MNPT to 3/4 Triple Barb Tee

SKU	Description
AT-12M16B	3/4 MNPT to 1 inch Triple Barb Tee



AML SERIES

The AML Series are MNPT by triple barbed elbows. This elbow is molded of NSF listed Natural Nylon or Black Polyethylene. Barbed fittings over one inch are not offered in Polyethylene. Optional materials include: Black Nylon, FDA listed Natural Polypropylene, and FDA listed Black Polypropylene. Combinations of these sizes are available: 1/8 inch, 3/16 inch, 1/4 inch, 5/16 inch, 3/8 inch, 1/2 inch, 5/8 inch, 3/4 inch, 1 inch, 1-1/4 inch, and 1-1/2 inch. Fittings over 1 inch are not available in Polyethylene.

SKU	Description
AML-6M10B-NN	3/8 inch MNPT by 5/8 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-6M10B-BPE	3/8 inch MNPT by 5/8 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-6M10B-NPP	3/8 inch MNPT by 5/8 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-6M10B-BPP	3/8 inch MNPT by 5/8 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-6M10B-BN	3/8 inch MNPT by 5/8 inch Black Nylon Triple Barbed Adapter Elbow
AML-6M6B-NN	3/8 inch MNPT by 3/8 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-6M6B-BPE	3/8 inch MNPT by 3/8 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-6M6B-NPP	3/8 inch MNPT by 3/8 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-6M6B-BPP	3/8 inch MNPT by 3/8 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-6M6B-BN	3/8 inch MNPT by 3/8 inch Black Nylon Triple Barbed Adapter Elbow
AML-6M4B-NN	3/8 inch MNPT by 1/4 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-6M4B-BPE	3/8 inch MNPT by 1/4 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-6M4B-NPP	3/8 inch MNPT by 1/4 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-6M4B-BPP	3/8 inch MNPT by 1/4 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-6M4B-BN	3/8 inch MNPT by 1/4 inch Black Nylon Triple Barbed Adapter Elbow
AML-6M8B-NN	3/8 inch MNPT by 1/2 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-6M8B-BPE	3/8 inch MNPT by 1/2 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-6M8B-NPP	3/8 inch MNPT by 1/2 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow

SKU	Description
AML-6M8B-BPP	3/8 inch MNPT by 1/2 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-6M8B-BN	3/8 inch MNPT by 1/2 inch Black Nylon Triple Barbed Adapter Elbow
AML-12M10B-NN	3/4 inch MNPT by 5/8 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-12M10B-BPE	3/4 inch MNPT by 5/8 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-12M10B-NPP	3/4 inch MNPT by 5/8 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-12M10B-BPP	3/4 inch MNPT by 5/8 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-12M10B-BN	3/4 inch MNPT by 5/8 inch Black Nylon Triple Barbed Adapter Elbow
AML-12M6LB-NN	3/4 inch MNPT by 3/8 inch NSF Natural Nylon Long Triple Barbed Adapter Elbow
AML-12M6LB-BPE	3/4 inch MNPT by 3/8 inch NSF Black Polyethylene Long Triple Barbed Adapter Elbow
AML-12M6LB-NPP	3/4 inch MNPT by 3/8 inch FDA Natural Polypropylene Long Triple Barbed Adapter Elbow
AML-12M6LB-BPP	3/4 inch MNPT by 3/8 inch FDA Black Polypropylene Long Triple Barbed Adapter Elbow
AML-12M6LB-BN	3/4 inch MNPT by 3/8 inch Black Nylon Long Triple Barbed Adapter Elbow
AML-12M12B-NN	3/4 inch MNPT by 3/4 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-12M12B-BPE	3/4 inch MNPT by 3/4 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-12M12B-NPP	3/4 inch MNPT by 3/4 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-12M12B-BPP	3/4 inch MNPT by 3/4 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-12M12B-BN	3/4 inch MNPT by 3/4 inch Black Nylon Triple Barbed Adapter Elbow
AML-12M16B-NN	3/4 inch MNPT by 1 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-12M16B-BPE	3/4 inch MNPT by 1 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-12M16B-NPP	3/4 inch MNPT by 1 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-12M16B-BPP	3/4 inch MNPT by 1 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-12M16B-BN	3/4 inch MNPT by 1 inch Black Nylon Triple Barbed Adapter Elbow
AML-12M4B-NN	3/4 inch MNPT by 1/4 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-12M4B-BPE	3/4 inch MNPT by 1/4 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-12M4B-NPP	3/4 inch MNPT by 1/4 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-12M4B-BPP	3/4 inch MNPT by 1/4 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-12M4B-BN	3/4 inch MNPT by 1/4 inch Black Nylon Triple Barbed Adapter Elbow
AML-12M8B-PVDF	3/4 inch MNPT by 1/2 inch PVDF Short Triple Barbed Adapter Elbow

PNEULINE SUPPLY INC.

SKU	Description
AML-12M8B-NN	3/4 inch MNPT by 1/2 inch NSF Natural Nylon Short Triple Barbed Adapter Elbow
AML-12M8LB-NN	3/4 inch MNPT by 1/2 inch NSF Natural Nylon Long Triple Barbed Adapter Elbow
AML-12M8B-BPE	3/4 inch MNPT by 1/2 inch NSF Black Polyethylene Short Triple Barbed Adapter Elbow
AML-12M8LB-BPE	3/4 inch MNPT by 1/2 inch NSF Black Polyethylene Long Triple Barbed Adapter Elbow
AML-12M8B-NPP	3/4 inch MNPT by 1/2 inch FDA Natural Polypropylene Short Triple Barbed Adapter Elbow
AML-12M8LB-NPP	3/4 inch MNPT by 1/2 inch FDA Natural Polypropylene Long Triple Barbed Adapter Elbow
AML-12M8B-BPP	3/4 inch MNPT by 1/2 inch FDA Black Polypropylene Short Triple Barbed Adapter Elbow
AML-12M8LB-BPP	3/4 inch MNPT by 1/2 inch FDA Black Polypropylene Long Triple Barbed Adapter Elbow
AML-12M8B-BN	3/4 inch MNPT by 1/2 inch Black Nylon Short Triple Barbed Adapter Elbow
AML-12M8LB-BN	3/4 inch MNPT by 1/2 inch Black Nylon Long Triple Barbed Adapter Elbow
AML-16M12B-NN	1 inch MNPT by 3/4 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-16M12B-BPE	1 inch MNPT by 3/4 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-16M12B-NPP	1 inch MNPT by 3/4 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-16M12B-BPP	1 inch MNPT by 3/4 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-16M12B-BN	1 inch MNPT by 3/4 inch Black Nylon Triple Barbed Adapter Elbow
AML-16M16B-NN	1 inch MNPT by 1 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-16M16B-BPE	1 inch MNPT by 1 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-16M16B-NPP	1 inch MNPT by 1 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-16M16B-BPP	1 inch MNPT by 1 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-16M16B-BN	1 inch MNPT by 1 inch Black Nylon Triple Barbed Adapter Elbow
AML-16M8B-NN	1 inch MNPT by 1/2 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-16M8B-BPE	1 inch MNPT by 1/2 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-16M8B-NPP	1 inch MNPT by 1/2 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-16M8B-BPP	1 inch MNPT by 1/2 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-16M8B-BN	1 inch MNPT by 1/2 inch Black Nylon Triple Barbed Adapter Elbow
AML-2M5B-NN	1/8 inch MNPT by 5/16 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-2M5B-BPE	1/8 inch MNPT by 5/16 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-2M5B-NPP	1/8 inch MNPT by 5/16 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-2M5B-BPP	1/8 inch MNPT by 5/16 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-2M5B-BN	1/8 inch MNPT by 5/16 inch Black Nylon Triple Barbed Adapter Elbow

SKU	Description
AML-2M3B-NN	1/8 inch MNPT by 3/16 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-2M3B-BPE	1/8 inch MNPT by 3/16 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-2M3B-NPP	1/8 inch MNPT by 3/16 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-2M3B-BPP	1/8 inch MNPT by 3/16 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-2M3B-BN	1/8 inch MNPT by 3/16 inch Black Nylon Triple Barbed Adapter Elbow
AML-2M6B-NN	1/8 inch MNPT by 3/8 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-2M6B-BPE	1/8 inch MNPT by 3/8 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-2M6B-NPP	1/8 inch MNPT by 3/8 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-2M6B-BPP	1/8 inch MNPT by 3/8 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-2M6B-BN	1/8 inch MNPT by 3/8 inch Black Nylon Triple Barbed Adapter Elbow
AML-2M4B-NN	1/8 inch MNPT by 1/4 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-2M4B-BPE	1/8 inch MNPT by 1/4 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-2M4B-NPP	1/8 inch MNPT by 1/4 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-2M4B-BPP	1/8 inch MNPT by 1/4 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-2M4B-BN	1/8 inch MNPT by 1/4 inch Black Nylon Triple Barbed Adapter Elbow
AML-4M5B-NN	1/4 inch MNPT by 5/16 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-4M5B-BPE	1/4 inch MNPT by 5/16 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-4M5B-NPP	1/4 inch MNPT by 5/16 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-4M5B-BPP	1/4 inch MNPT by 5/16 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-4M5B-BN	1/4 inch MNPT by 5/16 inch Black Nylon Triple Barbed Adapter Elbow
AML-4M3B-NN	1/4 inch MNPT by 3/16 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-4M3B-BPE	1/4 inch MNPT by 3/16 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-4M3B-NPP	1/4 inch MNPT by 3/16 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-4M3B-BPP	1/4 inch MNPT by 3/16 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-4M3B-BN	1/4 inch MNPT by 3/16 inch Black Nylon Triple Barbed Adapter Elbow
AML-4M6B-NN	1/4 inch MNPT by 3/8 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-4M6B-BPE	1/4 inch MNPT by 3/8 inch NSF Black Polyethylene Triple Barbed Adapter Elbow

SKU	Description
AML-4M6B-NPP	1/4 inch MNPT by 3/8 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-4M6B-BPP	1/4 inch MNPT by 3/8 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-4M6B-BN	1/4 inch MNPT by 3/8 inch Black Nylon Triple Barbed Adapter Elbow
AML-4M4B-NN	1/4 inch MNPT by 1/4 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-4M4B-BPE	1/4 inch MNPT by 1/4 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-4M4B-NPP	1/4 inch MNPT by 1/4 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-4M4B-BPP	1/4 inch MNPT by 1/4 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-4M4B-BN	1/4 inch MNPT by 1/4 inch Black Nylon Triple Barbed Adapter Elbow
AML-4M8B-NN	1/4 inch MNPT by 1/2 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-4M8B-BPE	1/4 inch MNPT by 1/2 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-4M8B-NPP	1/4 inch MNPT by 1/2 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-4M8B-BPP	1/4 inch MNPT by 1/2 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-4M8B-BN	1/4 inch MNPT by 1/2 inch Black Nylon Triple Barbed Adapter Elbow
AML-8M10LB-NN	1/2 inch MNPT by 5/8 inch NSF Natural Nylon Long Triple Barbed Adapter Elbow
AML-8M10LB-BPE	1/2 inch MNPT by 5/8 inch NSF Black Polyethylene Long Triple Barbed Adapter Elbow
AML-8M10LB-NPP	1/2 inch MNPT by 5/8 inch FDA Natural Polypropylene Long Triple Barbed Adapter Elbow
AML-8M10LB-BPP	1/2 inch MNPT by 5/8 inch FDA Black Polypropylene Long Triple Barbed Adapter Elbow
AML-8M10LB-BN	1/2 inch MNPT by 5/8 inch Black Nylon Long Triple Barbed Adapter Elbow
AML-8M6B-NN	1/2 inch MNPT by 3/8 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-8M6B-BPE	1/2 inch MNPT by 3/8 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-8M6B-NPP	1/2 inch MNPT by 3/8 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-8M6B-BPP	1/2 inch MNPT by 3/8 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-8M6B-BN	1/2 inch MNPT by 3/8 inch Black Nylon Triple Barbed Adapter Elbow
AML-8M12LB-NN	1/2 inch MNPT by 3/4 inch NSF Natural Nylon Long Triple Barbed Adapter Elbow
AML-8M12LB-NPP	1/2 inch MNPT by 3/4 inch FDA Natural Polypropylene Long Triple Barbed Adapter Elbow
AML-8M12LB-BPP	1/2 inch MNPT by 3/4 inch FDA Black Polypropylene Long Triple Barbed Adapter Elbow

SKU	Description
AML-8M12LB-BPE	1/2 inch MNPT by 3/4 inch Black Polyethylene Long Triple Barbed Adapter Elbow
AML-8M12LB-BN	1/2 inch MNPT by 3/4 inch Black Nylon Long Triple Barbed Adapter Elbow
AML-8M16B-NN	1/2 inch MNPT by 1 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-8M16B-BPE	1/2 inch MNPT by 1 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-8M16B-NPP	1/2 inch MNPT by 1 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-8M16B-BPP	1/2 inch MNPT by 1 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-8M16B-BN	1/2 inch MNPT by 1 inch Black Nylon Triple Barbed Adapter Elbow
AML-8M4B-NN	1/2 inch MNPT by 1/4 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-8M4B-BPE	1/2 inch MNPT by 1/4 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-8M4B-NPP	1/2 inch MNPT by 1/4 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-8M4B-BPP	1/2 inch MNPT by 1/4 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-8M4B-BN	1/2 inch MNPT by 1/4 inch Black Nylon Triple Barbed Adapter Elbow
AML-8M8B-NN	1/2 inch MNPT by 1/2 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-8M8B-BPE	1/2 inch MNPT by 1/2 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-8M8B-NPP	1/2 inch MNPT by 1/2 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-8M8B-BPP	1/2 inch MNPT by 1/2 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-8M8B-BN	1/2 inch MNPT by 1/2 inch Black Nylon Triple Barbed Adapter Elbow
AML-20M12B-NN	1-1/4 inch MNPT by 3/4 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-20M12B-BPE	1-1/4 inch MNPT by 3/4 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-20M12B-NPP	1-1/4 inch MNPT by 3/4 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-20M12B-BPP	1-1/4 inch MNPT by 3/4 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-20M12B-BN	1-1/4 inch MNPT by 3/4 inch Black Nylon Triple Barbed Adapter Elbow
AML-20M16B-NN	1-1/4 inch MNPT by 1 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-20M16B-BPE	1-1/4 inch MNPT by 1 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-20M16B-NPP	1-1/4 inch MNPT by 1 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-20M16B-BPP	1-1/4 inch MNPT by 1 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-20M16B-BN	1-1/4 inch MNPT by 1 inch Black Nylon Triple Barbed Adapter Elbow
AML-20M20B-NN	1-1/4 inch MNPT by 1-1/4 inch NSF Natural Nylon Triple Barbed Adapter Elbow

SKU	Description
AML-20M20B-BPE	1-1/4 inch MNPT by 1-1/4 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-20M20B-NPP	1-1/4 inch MNPT by 1-1/4 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-20M20B-BPP	1-1/4 inch MNPT by 1-1/4 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-20M20B-BN	1-1/4 inch MNPT by 1-1/4 inch Black Nylon Triple Barbed Adapter Elbow
AML-20M24B-NN	1-1/4 inch MNPT by 1-1/2 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-20M24B-BPE	1-1/4 inch MNPT by 1-1/2 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-20M24B-NPP	1-1/4 inch MNPT by 1-1/2 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-20M24B-BPP	1-1/4 inch MNPT by 1-1/2 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-20M24B-BN	1-1/4 inch MNPT by 1-1/2 inch Black Nylon Triple Barbed Adapter Elbow
AML-24M12B-NN	1-1/2 inch MNPT by 3/4 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-24M12B-BPE	1-1/2 inch MNPT by 3/4 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-24M12B-NPP	1-1/2 inch MNPT by 3/4 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-24M12B-BPP	1-1/2 inch MNPT by 3/4 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-24M12B-BN	1-1/2 inch MNPT by 3/4 inch Black Nylon Triple Barbed Adapter Elbow
AML-24M16B-NN	1-1/2 inch MNPT by 1 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-24M16B-BPE	1-1/2 inch MNPT by 1 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-24M16B-NPP	1-1/2 inch MNPT by 1 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-24M16B-BPP	1-1/2 inch MNPT by 1 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-24M16B-BN	1-1/2 inch MNPT by 1 inch Black Nylon Triple Barbed Adapter Elbow
AML-24M20B-NN	1-1/2 inch MNPT by 1-1/4 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-24M20B-BPE	1-1/2 inch MNPT by 1-1/4 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-24M20B-NPP	1-1/2 inch MNPT by 1-1/4 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow
AML-24M20B-BPP	1-1/2 inch MNPT by 1-1/4 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-24M20B-BN	1-1/2 inch MNPT by 1-1/4 inch Black Nylon Triple Barbed Adapter Elbow
AML-24M24B-NN	1-1/2 inch MNPT by 1-1/2 inch NSF Natural Nylon Triple Barbed Adapter Elbow
AML-24M24B-BPE	1-1/2 inch MNPT by 1-1/2 inch NSF Black Polyethylene Triple Barbed Adapter Elbow
AML-24M24B-NPP	1-1/2 inch MNPT by 1-1/2 inch FDA Natural Polypropylene Triple Barbed Adapter Elbow

SKU	Description
AML-24M24B-BPP	1-1/2 inch MNPT by 1-1/2 inch FDA Black Polypropylene Triple Barbed Adapter Elbow
AML-24M24B-BN	1-1/2 inch MNPT by 1-1/2 inch Black Nylon Triple Barbed Adapter Elbow



AM MULTI BARB THREADED ADAPTER

The AM Series is an MNPT by a triple barbed adapter. It is molded of NSF listed Natural Nylon or NSF listed Black Polyethylene. Optional materials are: Black Nylon, PVC, FDA listed Natural Polypropylene, and FDA listed Black Polypropylene. The MNPT threads sizes available are 1/8 inch, 1/4 inch, 3/8 inch, 1/2 inch, 3/4 inch, 1 inch, 1-1/4 inch, 1-1/2 inch, and 2 inches. The barb sizes are 3/16 inch, 1/4 inch, 5/16 inch, 3/8 inch, 5/32 inch, 1 inch, 1-1/4 inch, and 1-1/2 inch. Barbed fittings over one inch are not offered in Polyethylene. The temperature range is -40° F to 200° F and the maximum working pressure is 125 psi.

SKU	Description
AM-2M532B	Adapter 1/8 MNPT 5/32 Barb
AM-2M3B	Adapter 1/8 MNPT 3/16 Barb
AM-2M4B	Adapter 1/8 MNPT 1/4 Barb
AM-2M5B	Adapter 1/8 MNPT 5/16 Barb
AM-2M6B	Adapter 1/8 MNPT 3/8 Barb
AM-2M8B	Adapter 1/8 MNPT 1/2 Barb
AM-32M32B	Adapter 2 inch MNPT 2 inch Barb
AM-4M532B	Adapter 1/4 MNPT by 5/32 Barb
AM-4M3B	Adapter 1/4 MNPT 3/16 Barb
AM-4M4B	Adapter 1/4 MNPT 1/4 Barb
AM-4M5B	Adapter 1/4 MNPT 5/16 Barb
AM-4M6B	Adapter 1/4 MNPT 3/8 Barb
AM-4M8B	Adapter 1/4 MNPT 1/2 Barb
AM-6M4B	Adapter 3/8 MNPT 1/4 Barb
AM-6M5B	Adapter 3/8 MNPT 5/16 Barb
AM-6M6B	Adapter 3/8 MNPT 3/8 Barb
AM-6M8B	Adapter 3/8 MNPT 1/2 Barb
AM-6M10B	Adapter 3/8 MNPT 5/8 Barb
AM-8M3B	Adapter 1/2 MNPT 3/16 Barb
AM-8M4B	Adapter 1/2 MNPT 1/4 Barb
AM-8M6B	Adapter 1/2 MNPT 3/8 Barb
AM-8M8B	Adapter 1/2 MNPT 1/2 Barb
AM-8M10B	Adapter 1/2 MNPT 5/8 Barb
AM-8M12B	Adapter 1/2 MNPT 3/4 Barb
AM-8M16B	Adapter 1/2 MNPT 1 inch Barb

SKU	Description
AM-12M4B	Adapter 3/4 MNPT 1/4 Barb
AM-12M6B	Adapter 3/4 MNPT 3/8 Barb
AM-12M8B	Adapter 3/4 MNPT 1/2 Barb
AM-12M10B	Adapter 3/4 MNPT 5/8 Barb
AM-12M12B	Adapter 3/4 MNPT 3/4 Barb
AM-12M16B	Adapter 3/4 MNPT 1 inch Barb
AM-16M8B	Adapter 1 inch MNPT by 1/2 inch Barb
AM-16M12B	Adapter 1 inch MNPT 3/4 Barb
AM-16M16B	Adapter 1 inch MNPT 1 inch Barb
AM-16M20B	Adapter 1 inch MNPT 1-1/4 inch Barb
AM-16M24B	Adapter 1 inch MNPT 1-1/2 inch Barb
AM-20M12B	Adapter 1-1/4 inch MNPT 3/4 Barb
AM-20M16B	Adapter 1-1/4 inch MNPT 1 inch Barb
AM-20M20B	Adapter 1-1/4 inch MNPT 1-1/4 Barb
AM-20M24B	Adapter 1-1/4 inch MNPT 1-1/2 inch Barb
AM-24M12B	Adapter 1-1/2 inch MNPT 3/4 Barb
AM-24M16B	Adapter 1-1/2 inch MNPT 1 inch Barb
AM-24M20B	Adapter 1-1/2 inch MNPT 1-1/4 inch Barb
AM-24M24B	Adapter 1-1/2 inch MNPT 1-1/2 inch Barb
AM-24M32B	Adapter 1-1/2 inch MNPT by 2 inch Barb



AFL FEMALE MULTI BARBED ELBOW ADAPTER

The AFL Series is an FNPT by a triple barb elbow, and is molded of NSF listed Natural Nylon or FDA listed Black Polypropylene. FNPT sizes are: 1/8 inch, 1/4 inch, 3/8 inch, 1/2 inch, and 3/4 inch. Barb sizes are: 1/4 inch, 3/8 inch, 1/2 inch, 5/8 inch, and 3/4 inch. The working pressure for both materials is 150 psi. These adapters should not be used for compressed gasses.

SKU	DESCRIPTION
AFL-2F4B	1/8 FNPT by 1/4 Barb Elbow Adapter
AFL-2F6B	1/8 FNPT by 3/8 Barb Elbow Adapter
AFL-4F4B	1/4 FNPT by 1/4 Barb Elbow Adapter
AFL-4F6B	1/4 FNPT by 3/8 Barb Elbow Adapter
AFL-4F8B	1/4 FNPT by 1/2 Barb Elbow Adapter
AFL-6F10B	3/8 FNPT by 5/8 Barb Elbow Adapter
AFL-6F4B	3/8 FNPT by 1/4 Barb Elbow Adapter
AFL-6F6B	3/8 FNPT by 3/8 Barb Elbow Adapter

SKU	DESCRIPTION
AFL-6F8B	3/8 FNPT by 1/2 Barb Elbow Adapter
AFL-8F10B	1/2 FNPT by 5/8 Barb Elbow Adapter
AFL-8F4B	1/2 FNPT by 1/4 Barb Elbow Adapter
AFL-8F6B	1/2 FNPT by 3/8 Barb Elbow Adapter
AFL-8F8B	1/2 FNPT by 1/2 Barb Elbow Adapter

INDEX

A

AFL FEMALE MULTI BARBED ELBOW ADAPTER 18

AM MULTI BARB THREADED ADAPTER 17

AML Series 10

AT Series 9

C

C MULTI-BARB EQUAL REDUCING CONNECTOR 5

CR Series 5

D

DCE Series 4

G

GEN1 Series Barbed Fittings 2

L

LGH Series 1